


**DIN 466**  
**Knurled nuts**

High version

Stainless steel 1.4305 | Cr(VI)-free | Metric thread



Diameter (d)	da		nominal size	dk		ds		h		k		r nominal size	Pitch (P)
	min.	max.		min.	max.	min.	max.	min.	max.	min.	max.		
M2	2.0	2.30	9	8.71	9.29	4.20	4.5	5.00	5.3	1.75	2.0	0.5	0.40
M2.5	2.5	2.90	11	10.65	11.35	4.70	5.0	6.14	6.5	2.25	2.5	0.5	0.45
M3	3.0	3.45	12	11.65	12.35	5.70	6.0	7.14	7.5	2.25	2.5	0.5	0.50
M4	4.0	4.60	16	15.65	16.35	7.64	8.0	9.14	9.5	3.20	3.5	0.5	0.70
M5	5.0	5.75	20	19.58	20.42	9.64	10.0	11.07	11.5	3.70	4.0	1	0.80
M6	6.0	6.75	24	23.58	24.42	11.57	12.0	14.57	15.0	4.70	5.0	1	1.00
M8	8.0	8.75	30	29.58	30.42	15.57	16.0	17.57	18.0	5.70	6.0	2	1.25
M10	10.0	10.80	36	35.50	36.50	19.48	20.0	22.48	23.0	7.64	8.0	2	1.50

All technical data refer to the measure mm

