## All technical data refer to the measure mm


## **DIN 6319 D**

## **Conical cups**

Form D: with d4 = d3 | hardened

Steel | bright | Cr(VI)-free





Diameter	d <sub>2</sub>	d <sub>4</sub>	d <sub>5</sub>	h <sub>3</sub>
(d)	nominal size			nominal size
7.1	7.1	12	11.0	2.8
9.6	9.6	17	14.5	3.5
12	12	21	18.5	4.2
14.2	14.2	24	20.0	5.0
19	19	28	26.0	5.6
23.2	23.2	30	31.0	6.2
28	28	36	37.0	7.5
35	35	44	49.0	9.5
42	42	56	60.0	12.0
49	49	68	70.0	15.0