


DIN 6340

Washers

For clamping tools | tempered

Steel HV 30 | bright | Cr(VI)-free



Diameter (d)	d ₁ nominal size	d ₂ nominal size	s nominal size
6.4	6.4	17	3
8.4	8.4	23	4
10.5	10.5	28	4
13	13	35	5
17	17	45	6
21	21	50	6
25	25	60	8
31	31	68	10

All technical data refer to the measure mm

