
DIN 906

Locking screws

Hexagon socket

Steel | zinc-plated | Cr(VI)-free | Conical Whitworth pipe thread





Diameter	I_{1}	е	s	t ₁	w	Tool
(d)		min.	nominal size	min.	min.	size
R 1/8	8	5.7	5	4	1.8	SW 5
R 1/4	10	8.0	7	5	2.0	SW 7
R 3/8	10	9.2	8	5	2.0	SW 8
R 1/2	10	11.4	10	5	2.0	SW 10
R 3/4	12	13.7	12	6	2.0	SW 12