

**E 1423**

**EJOT®-PT screws**

Countersunk head | cross-slot phillips

Steel 10 | zinc-plated | Cr(VI)-free | Self-tapping thread

Further information: For further information and CAD-files please follow the link to the EJOT-homepage:

<http://www.ejot.com/industry>

Diameter (d)	c max.	d <sub>1</sub> nominal size	r nominal size	Pitch (P)	t		Tool size
					max.	min.	
2.5	0.55	2.5	1	1.12	1.0	0.80	T8
3	0.55	3	1.2	1.34	1.0	0.80	T8
3.5	0.65	3.5	1.4	1.57	1.3	1.00	T15
4	0.70	4	1.6	1.79	1.7	1.25	T20

Length (l) nominal size
10
16

Diameter (d)	Length (l)		
	8	10	16
2.5	●	●	
3	●	●	
3.5			●
4		●	

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

