

E 1451
EJOT®-PT screws

Button head | torx drive

Stainless steel A2 | Cr(VI)-free | Self-tapping thread

Further information: For further information and CAD-files please follow the link to the EJOT-homepage:

<http://www.ejot.com/industry>

Diameter (d)	d ₁ nominal size	r nominal size	s nominal size	Pitch (P)	t		K	Tool size
					max.	min.		
3	3	0.4	0.6	1.34	1.30	1.0	2.1	10 IP
4	4	0.5	0.8	1.79	1.65	1.3	2.6	20 IP

Length (l) nominal size
6
10
12
16
20
25

Diameter (d)	Length (l)					
	6	10	12	16	20	25
3	●	●	●		●	
4			●	●		●

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

