

**E 5452**

**EJOT®-Delta PT-screws**

Linsenkopf | Torx-Plus / Autosert

Steel 10 | zinc-plated | Cr(VI)-free | Self-tapping thread

Further information: For further information and CAD-files please follow the link to the

EJOT-homepage:

<http://www.ejot.com/industry>

Diameter (d)	d <sub>1</sub> nominal size	r max.	Pitch (P)	t		Tool size
				max.	min.	
2	2	0.35	0.78	0.85	0.65	T6 (1,75)
2.2	2.2	0.35	0.85	0.85	0.65	T6 (1,75)
2.5	2.5	0.40	0.95	1.00	0.80	T8 (2,4)
3	3	0.50	1.12	1.30	1.00	T10 (2,8)
3.5	3.5	0.50	1.29	1.50	1.00	T15 (3,35)
4	4	0.60	1.46	1.80	1.40	T20 (3,95)
5	5	0.70	1.80	1.90	1.50	T25 (4,5)
6	6	0.80	2.14	2.40	1.90	T30 (5,6)

Length (l) nominal size
4
5
6
7
8
10
12
14

Length (l) nominal size
16
18
20
25
30

Diameter (d)	Length (l)												
	4	5	6	7	8	10	12	14	16	18	20	25	30
2	●		●		●								
2.2			●		●	●							
2.5		●	●		●	●	●						
3			●	●	●	●		●	●		●	●	
3.5						●							
4						●	●		●	●	●	●	
5							●		●		●		●
6									●		●		

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

