## **ISO 4014** similar to DIN 931

## **Hexagon head bolts**


Hexagon head | with body


Steel 8.8 | zinc-plated | Cr(VI)-free | Metric thread

Further information: DIN-standard has been withdrawn  $\mid$  changed spanner widths for M10, M12, M14 and M22

There is a separation into product classes A and B, with the data sheet showing the largest range of values. For more information, see the technical details of the selected article.







Diameter		b		(		d <sub>a</sub>	d <sub>s</sub>	d <sub>w</sub>
(d)	l up to 125	I up to 200	l longer than 200	min.	max.	max.	max.	min.
M8	22	28	41	0.15	0.6	9.2	8	11.47
M10	26	32	45	0.15	0.6	11.2	10	14.47
M12	30	36	49	0.15	0.6	13.7	12	16.47
M14	34	40	53	0.15	0.6	15.7	14	19.15
M16	38	44	57	0.20	0.8	17.7	16	22.00
M24	54	60	73	0.20	0.8	26.4	24	33.25

Diameter	е		k		r			Pitch	Tool
(d)	min.	nominal size	min.	max.	min.	max.	min.	(P)	size
M8	14.20	5.3	5.15	5.45	0.4	13	12.57	1.25	SW 13
M10	17.59	6.4	6.11	6.69	0.4	16	15.57	1.50	SW 16
M12	19.85	7.5	7.21	7.79	0.6	18	17.57	1.75	SW 18
M14	22.78	8.8	8.51	9.09	0.6	21	20.16	2.00	SW 21
M16	26.17	10.0	9.82	10.18	0.6	24	23.16	2.00	SW 24
M24	39.55	15.0	14.78	15.22	0.8	36	35.00	3.00	SW 36

communication of its content only permitted with express consert.

## All technical data refer to the measure mm

**ISO 4014** similar to DIN 931

## **Hexagon head bolts**

Hexagon head | with body

Steel 8.8 | zinc-plated | Cr(VI)-free | Metric thread

Length (I)											
nominal size	min.	max.									
45	43.75	46.25									
50	48.75	51.25									
55	53.50	56.50									
60	58.50	61.50									
65	63.50	66.50									
70	68.50	71.50									
75	73.50	76.50									
80	78.50	81.50									

Length (I)										
nominal size	min.	max.								
85	83.25	86.75								
90	88.25	91.75								
95	93.25	96.75								
100	98.25	101.75								
110	108.25	111.75								
120	118.25	121.75								
130	128.00	132.00								
140	138.00	142.00								

Length (I)										
nominal size	min.	max.								
150	148.00	152.00								
160	158.00	162.00								
180	178.00	182.00								

Diameter	Length (I)																		
(d)	45	50	55	60	65	70	75	80	85	90	95	100	110	120	130	140	150	160	180
M8	•																		
M10	•	•	•	•	•	•	•	•		•		•	•		•	•			
M12	•	•	•	•	•	•				•	•	•							•
M14												•	•	•	•	•			
M16												•							
M24								•											

<sup>•</sup> Combinations available in the eShop | Other sizes on request