

## **Hexagon nuts**

Steel 10 | zinc-plated, thick-film passivated (VZD) | Contains Cr(VI) | Metric thread

Further information: ISO-standard has been withdrawn | changed spanner widths for M10, M12, M14 and M22 | changed head height | the fine thread has been transferred to ISO 8673







Diameter	d <sub>a</sub>		d <sub>w</sub>	е	m		S		Pitch	Tool
(d)	min.	max.	min.	min.	min.	max.	min.	max.	(P)	size
M6	6	6.75	8.9	11.05	4.90	5.2	9.78	10	1.00	SW 10
M8	8	8.75	11.6	14.38	6.44	6.8	12.73	13	1.25	SW 13
M10	10	10.80	14.6	17.77	8.04	8.4	15.73	16	1.50	SW 16
M12	12	13.00	16.6	20.03	10.37	10.8	17.73	18	1.75	SW 18
M14	14	15.10	19.6	23.36	12.10	12.8	20.67	21	2.00	SW 21
M16	16	17.30	22.5	26.75	14.10	14.8	23.67	24	2.00	SW 24
M20	20	21.60	27.7	32.95	16.90	18.0	29.16	30	2.50	SW 30
M24	24	25.90	33.3	39.55	20.20	21.5	35.00	36	3.00	SW 36