

ISO 7380-2

Round head screws

Halbrundkopf mit Flansch | Innensechskant

Steel 10.9 | zinc-plated, thick-film passivated (VZD) | Cr(VI)-free | Metric thread



Diameter (d)	b nominal size	c		d _a max.	d _c		d _k		d _s	
		min.	max.		min.	max.	min.	max.	min.	max.
6	24	1.00	1.2	6.8	12.9	13.6	9.6	10.0	5.82	6
8	24	1.25	1.5	9.2	17.1	17.8	12.8	13.2	7.78	8

Diameter (d)	d _w min.	k		e min.	s			Pitch (P)	w min.
		min.	max.		nominal size	min.	max.		
6	12.2	3.0	3.3	4.58	4	4.02	4.10	1.00	0.74
8	16.4	4.1	4.4	5.72	5	5.02	5.14	1.25	1.05

Length (l)	
nominal size	
12	
16	
20	
25	

Diameter (d)	Length (l)			
	12	16	20	25
6	●	●	●	
8				●

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm