

RIVKLE® Mandrel

Spare threaded mandrel for the RIVKLE® M2007 hand-held setting tool.

Technical information can be found on the last page.



Diameter (d)	Article number	For tool type
M 5	23530205020	M2007
M 6	23530206020	M2007
M 8	23530208020	M2007
M 10	23530210020	M2007
M 12	23530212020	M2007

All technical data refer to the measure mm






Head diameter
Overall length
Thread size




Grip range

Defines the range of total thickness of the customers part (even if it consists of more than one layer)



Hole geometry

If round → diameter
If hexagonal → wigth across flats



Head projection after setting

Variable according to the application (setting load, material substrate, etc.)


Blind side projection after installation

Defines the clearance needed on the blind side (cannot be used for quality control)


Setting stroke

Difference of total length before and after installation

RIVKLE® Nut



RIVKLE® Stud



- RIVKLE®
- Mandrel*
- Customers part
- Anvil*
- Counter nut
- Setting tool

in accordance to chosen RIVKLE®

All technical data refer to the measure mm

