All technical data refer to the measure mm

RIVKLE® PNP Standard blind rivet nuts


Steel zinc-plated | Flat head | Slotted | Cylindrical | Open


Note: need specific mandrel (longer)

Technical information can be found on the last page.




Diameter	Article number	Drilling diameter d				Е	L ₂	е		Length (I)
(d)		min.	max.	В	D	nominal size		min.	max.	nominal size
M 5	66870511030	7.48	7.62	12.7	7.47	1	9.9	0.5	3	22.0
M 6	66870611050	8.80	8.93	15.9	8.79	1.5	12.8	0.5	5	26.9
M 8	66870811050	11.11	11.50	19.0	11.10	1.5	14.5	0.5	5	30.5






Grip range

Defines the range of total thickness of the customers part (even if it consists of more than one layer)



Hole geometry

If round -> diameter If hexagonal -> wigth across flats



Difference of total length before and after installation



in accordance to chosen RIVKLE®

