
All technical data refer to the measure mm

SNAPLOC® Ball studs

In clip form





Article number	Outer dimension	Depth (L1)	Colour	Thread dimensions	Ball diameter (D)
40010823084	8 mm x 10 mm	9	black	2 - 2.3 mm	8
40090181301	d = 10 mm	11	black	2 - 3 mm	7