


DIN 439 similar to ISO 4035

Hexagon nuts

Low version | Form B: with chamfer

Steel 04 | zinc-plated | Cr(VI)-free | Metric thread

Further information: DIN-standard has been withdrawn | different spanner widths for M10, M12, M14 and M22 | only the regular thread is included in ISO 4035 | the fine thread was transferred to ISO 8675



Diameter (d)	da		dw min.	e min.	m		s		Pitch (P)	Tool size
	min.	max.			min.	max.	min.	max.		
M2	2	2.30	3.1	4.32	0.95	1.2	3.82	4.0	0.40	SW 4
M3	3	3.45	4.6	6.01	1.55	1.8	5.32	5.5	0.50	SW 5,5
M4	4	4.60	5.9	7.66	1.95	2.2	6.78	7.0	0.70	SW 7
M5	5	5.75	6.9	8.79	2.45	2.7	7.78	8.0	0.80	SW 8
M6	6	6.75	8.9	11.05	2.90	3.2	9.78	10.0	1.00	SW 10
M8	8	8.75	11.6	14.38	3.70	4.0	12.73	13.0	1.25	SW 13
M10	10	10.80	15.6	18.90	4.70	5.0	16.73	17.0	1.50	SW 17
M12	12	13.00	17.4	21.10	5.70	6.0	18.67	19.0	1.75	SW 19
M14	14	15.10	20.5	24.49	6.42	7.0	21.67	22.0	2.00	SW 22
M16	16	17.30	22.5	26.75	7.42	8.0	23.67	24.0	2.00	SW 24
M18	18	19.50	24.9	29.56	8.42	9.0	26.16	27.0	2.50	SW 27
M20	20	21.60	27.7	32.95	9.10	10.0	29.16	30.0	2.50	SW 30
M22	22	23.80	29.5	35.03	9.90	11.0	31.00	32.0	2.50	SW 32
M24	24	25.90	33.2	39.55	10.90	12.0	35.00	36.0	3.00	SW 36
M27	27	29.20	38.0	45.20	12.40	13.5	40.00	41.0	3.00	SW 41
M30	30	32.40	42.7	50.85	13.90	15.0	45.00	46.0	3.50	SW 46

All technical data refer to the measure mm

