


**DIN 1440** similar to ISO 8738

## Washers

Medium version | for studs

Stainless steel A4 | Cr(VI)-free

Further information: DIN standard has been withdrawn



| Diameter<br>(d) | d <sub>1</sub><br>nominal size | d <sub>2</sub><br>nominal size | s<br>nominal size |
|-----------------|--------------------------------|--------------------------------|-------------------|
| 3               | 3                              | 6                              | 0.8               |
| 4               | 4                              | 8                              | 0.8               |
| 5               | 5                              | 10                             | 0.8               |
| 6               | 6                              | 12                             | 1.6               |
| 7               | 7                              | 14                             | 1.6               |
| 8               | 8                              | 16                             | 2.0               |
| 12              | 12                             | 25                             | 3.0               |
| 13              | 13                             | 25                             | 3.0               |
| 14              | 14                             | 28                             | 3.0               |
| 16              | 16                             | 28                             | 3.0               |
| 18              | 18                             | 30                             | 4.0               |
| 20              | 20                             | 32                             | 4.0               |
| 22              | 22                             | 34                             | 4.0               |
| 23              | 23                             | 36                             | 4.0               |
| 24              | 24                             | 38                             | 4.0               |
| 25              | 25                             | 40                             | 4.0               |
| 26              | 26                             | 40                             | 5.0               |
| 27              | 27                             | 40                             | 5.0               |
| 28              | 28                             | 42                             | 5.0               |
| 30              | 30                             | 45                             | 5.0               |
| 32              | 32                             | 50                             | 5.0               |
| 33              | 33                             | 50                             | 5.0               |
| 36              | 36                             | 52                             | 6.0               |
| 40              | 40                             | 58                             | 6.0               |

All technical data refer to the measure mm

