


DIN 7603

Sealing rings

Form A: flat sealing ring

Copper | Cr(VI)-free



Diameter (d)	d ₁		d ₂		h		
	min.	max.	min.	max.	nominal size	min.	max.
4 x 6	4.2	4.5	5.7	5.9	1.0	0.8	1.2
4 x 8	4.2	4.5	7.7	7.9	1.0	0.8	1.2
5 x 7.5	5.2	5.5	7.2	7.4	1.0	0.8	1.2
5.5 x 8	5.7	6.0	7.7	7.9	1.0	0.8	1.2
6.5 x 9.5	6.7	7.0	9.2	9.4	1.0	0.8	1.2
8 x 11.5	8.2	8.5	11.2	11.4	1.0	0.8	1.2
8 x 12	8.2	8.5	11.7	11.9	1.0	0.8	1.2
10 x 13.5	10.2	10.5	13.2	13.4	1.0	0.8	1.2
10 x 14	10.2	10.5	13.7	13.9	1.0	0.8	1.2
12 x 15.5	12.2	12.5	15.2	15.4	1.5	1.3	1.7
12 x 16	12.2	12.5	15.7	15.9	1.5	1.3	1.7
12 x 17	12.2	12.5	16.7	16.9	1.5	1.3	1.7
12 x 18	12.2	12.5	17.7	17.9	1.5	1.3	1.7
12 x 19	12.2	12.5	18.7	18.9	1.5	1.3	1.7
14 x 18	14.2	14.5	17.7	17.9	1.5	1.3	1.7
14 x 20	14.2	14.5	19.7	19.9	1.5	1.3	1.7
15 x 23	15.2	15.5	22.7	22.9	1.5	1.3	1.7
16 x 20	16.2	16.5	19.7	19.9	1.5	1.3	1.7
16 x 22	16.2	16.5	21.7	21.9	1.5	1.3	1.7
17 x 21	17.2	17.5	20.7	20.9	1.5	1.3	1.7
17 x 23	17.2	17.5	22.7	22.9	1.5	1.3	1.7
18 x 22	18.2	18.5	21.7	21.9	1.5	1.3	1.7
18 x 24	18.2	18.5	23.7	23.9	1.5	1.3	1.7
20 x 24	20.2	20.5	23.7	23.9	1.5	1.3	1.7
20 x 26	20.2	20.5	25.7	25.9	1.5	1.3	1.7
21 x 26	21.2	21.5	25.7	25.9	1.5	1.3	1.7
22 x 27	22.2	22.5	26.7	26.9	1.5	1.3	1.7
22 x 29	22.2	22.5	28.7	28.9	1.5	1.3	1.7
24 x 29	24.3	24.6	28.7	28.9	2.0	1.8	2.2
24 x 30	24.3	24.6	29.7	29.9	2.0	1.8	2.2
25 x 30	25.3	25.6	29.7	29.9	2.0	1.8	2.2
26 x 31	26.3	26.6	30.7	30.9	2.0	1.8	2.2

All technical data refer to the measure mm



DIN 7603

Sealing rings

Form A: flat sealing ring

Copper | Cr(VI)-free

Diameter (d)	d ₁		d ₂		h		
	min.	max.	min.	max.	nominal size	min.	max.
26 x 32	26.3	26.6	31.7	31.9	2.0	1.8	2.2
27 x 32	27.3	27.6	31.7	31.9	2.0	1.8	2.2
30 x 36	28.3	28.6	35.7	35.9	2.0	1.8	2.2
30 x 38	30.3	30.6	37.7	37.9	2.0	1.8	2.2
32 x 38	30.3	30.6	37.7	37.9	2.0	1.8	2.2
33 x 39	33.3	33.6	38.7	38.9	2.0	1.8	2.2
35 x 41	35.3	35.6	40.7	40.9	2.0	1.8	2.2
36 x 42	36.3	36.6	41.7	41.9	2.0	1.8	2.2
38 x 44	38.3	38.6	43.7	43.9	2.0	1.8	2.2
39 x 46	39.3	39.6	45.7	45.9	2.0	1.8	2.2
42 x 49	42.3	42.6	48.7	48.9	2.0	1.8	2.2
45 x 52	45.3	45.6	51.7	51.9	2.0	1.8	2.2
48 x 55	48.3	48.6	54.7	54.9	2.0	1.8	2.2
52 x 60	52.5	53.0	59.5	59.8	2.5	2.3	2.7
57 x 63	56.5	57.0	56.5	56.8	2.5	2.3	2.7
60 x 68	60.5	61.0	67.5	67.8	2.5	2.3	2.7
64 x 72	64.5	65.0	71.5	71.8	2.5	2.3	2.7

All technical data refer to the measure mm

