


**DIN 934** similar to ISO 4032

## Hexagon nuts

External hex

Brass | nickel plated | Cr(VI)-free | Metric thread

Further information: DIN-standard has been withdrawn | changed spanner widths for M10, M12, M14 and M22 | the fine thread has been transferred to ISO 8673



Diameter (d)	d <sub>a</sub>		d <sub>w</sub>	e	m		s		Pitch (P)	Tool size
	min.	max.			min.	max.	min.	max.		
M2	2.0	2.30	3.2	4.32	1.35	1.6	3.82	4.0	0.40	SW 4
M2.5	2.5	2.90	4.1	5.45	1.75	2.0	4.82	5.0	0.45	SW 5
M3	3.0	3.45	4.5	6.01	2.15	2.4	5.32	5.5	0.50	SW 5,5
M3.5	3.5	4.00	5.0	6.58	2.55	2.8	5.82	6.0	0.60	SW 6
M4	4.0	4.60	5.8	7.66	2.90	3.2	6.78	7.0	0.70	SW 7
M5	5.0	5.75	6.8	8.79	3.70	4.0	7.78	8.0	0.80	SW 8
M6	6.0	6.75	8.8	11.05	4.70	5.0	9.78	10.0	1.00	SW 10
M8	8.0	8.75	11.3	14.38	6.14	6.5	12.73	13.0	1.25	SW 13
M10	10.0	10.80	15.3	18.90	7.64	8.0	16.73	17.0	1.50	SW 17
M12	12.0	13.00	17.2	21.10	9.64	10.0	18.67	19.0	1.75	SW 19
M16	16.0	17.30	22.2	26.75	12.30	13.0	23.67	24.0	2.00	SW 24
M20	20.0	21.60	28.2	32.95	14.90	16.0	29.16	30.0	2.50	SW 30
M30	30.0	32.40	42.7	50.85	22.70	24.0	45.00	46.0	3.50	SW 46

All technical data refer to the measure mm

