


ISO 4032 similar to DIN 934

Hexagon nuts

Stainless steel A4 | Cr(VI)-free | Metric thread

Further information: ISO-standard has been withdrawn | changed spanner widths for M10, M12, M14 and M22 | changed head height | the fine thread has been transferred to ISO 8673



Diameter (d)	d _a		d _w min.	e min.	m		s		Pitch (P)	Tool size
	min.	max.			min.	max.	min.	max.		
M5	5	5.75	6.9	8.79	4.40	4.7	7.78	8	0.80	SW 8
M6	6	6.75	8.9	11.05	4.90	5.2	9.78	10	1.00	SW 10
M8	8	8.75	11.6	14.38	6.44	6.8	12.73	13	1.25	SW 13
M10	10	10.80	14.6	17.77	8.04	8.4	15.73	16	1.50	SW 17
M12	12	13.00	16.6	20.03	10.37	10.8	17.73	18	1.75	SW 19
M16	16	17.30	22.5	26.75	14.10	14.8	23.67	24	2.00	SW 24
M20	20	21.60	27.7	32.95	16.90	18.0	29.16	30	2.50	SW 30
M24	24	25.90	33.3	39.55	20.20	21.5	35.00	36	3.00	SW 36

All technical data refer to the measure mm

