


DIN 936

Hexagon nuts

Low form | external hex

Steel 17 H | zinc-plated | Cr(VI)-free | Metric fine thread

Further information: Norm has been withdrawn without replacement



| Diameter<br>(d) | d <sub>a</sub> |       | d <sub>w</sub> | e     | m     |      | s     |      | Pitch<br>(P) | Tool<br>size |
|-----------------|----------------|-------|----------------|-------|-------|------|-------|------|--------------|--------------|
|                 | min.           | max.  |                |       | min.  | max. | min.  | max. |              |              |
| M8 x 1          | 8              | 8.75  | 11.3           | 14.38 | 4.70  | 5    | 12.73 | 13   | 1.0          | SW 13        |
| M10 x 1         | 10             | 10.80 | 15.3           | 18.90 | 5.70  | 6    | 16.73 | 17   | 1.0          | SW 17        |
| M12 x 1.5       | 12             | 13.00 | 17.2           | 21.10 | 6.64  | 7    | 18.67 | 19   | 1.5          | SW 19        |
| M14 x 1.5       | 14             | 15.10 | 20.2           | 24.49 | 7.42  | 8    | 21.67 | 22   | 1.5          | SW 22        |
| M16 x 1.5       | 16             | 17.30 | 22.2           | 26.75 | 7.42  | 8    | 23.67 | 24   | 1.5          | SW 24        |
| M18 x 1.5       | 18             | 19.50 | 25.3           | 29.56 | 8.42  | 9    | 26.16 | 27   | 1.5          | SW 27        |
| M20 x 1.5       | 20             | 21.60 | 28.2           | 32.95 | 8.10  | 9    | 29.16 | 30   | 1.5          | SW 30        |
| M20 x 2         | 20             | 21.60 | 28.2           | 32.95 | 8.10  | 9    | 29.16 | 30   | 2.0          | SW 30        |
| M22 x 1.5       | 22             | 23.70 | 29.5           | 35.03 | 9.10  | 10   | 31.00 | 32   | 1.5          | SW 32        |
| M22 x 2         | 22             | 23.70 | 29.5           | 35.03 | 9.10  | 10   | 31.00 | 32   | 2.0          | SW 32        |
| M24 x 1.5       | 24             | 25.90 | 33.2           | 39.55 | 9.10  | 10   | 35.00 | 36   | 1.5          | SW 36        |
| M27 x 1.5       | 27             | 29.10 | 38.0           | 45.20 | 10.90 | 12   | 40.00 | 41   | 1.5          | SW 41        |
| M27 x 2         | 27             | 29.10 | 38.0           | 45.20 | 10.90 | 12   | 40.00 | 41   | 2.0          | SW 41        |
| M30 x 1.5       | 30             | 32.40 | 42.7           | 50.85 | 10.90 | 12   | 45.00 | 46   | 1.5          | SW 46        |

All technical data refer to the measure mm

