All technical data refer to the measure mm

RIVKLE® HRT Blind rivet nuts


Steel zinc-plated | Flat head | Hexagonal | Hexagonal | Open


Note: Thread according to ISO 6h (ISO 68-1) -Equivalent nut class 10 or 12 (compatible screw class 10,9 or 12,9)

Technical information can be found on the last page.




Diameter	Article number	Drilling diameter d		Е	L ₂	е		Length (I)	
(d)		nominal size	В	nominal size		min.	max.	nominal size	S
M 8	23249080502	11	17	1.5	16.0	3	6.0	26.6	S = 9.6 - e
M 10	23291100501	13	24	2	18.0	2	5.0	28.5	S = 9.5 - e
	23291100503		20		17.5	1	3.5	27.0	S = 8.7 - e
M 12x1.5	23291124501	16	27	2	22.0	1	4.0	33.0	S = 10.5 - e






Grip range

Defines the range of total thickness of the customers part (even if it consists of more than one layer)



Hole geometry

If round -> diameter
If hexagonal -> wigth across flats





in accordance to chosen RIVKLE®

