

DIN 939
Studs


Threaded end $\approx 1,25 d$

Steel 8.8 | zinc-plated | Cr(VI)-free | Metric thread



Einschraubende

Mutterende



Diameter (d)	b			b ₁ nominal size	Pitch (P)	z ₂	z ₁
	l up to 125	l up to 200	l longer than 200				
M6	18	24	–	7.5	1.00	1.25	5.5
M8	22	28	–	10.0	1.25	1.60	3.2
M10	26	32	45	12.0	1.50	1.90	3.8
M12	30	36	49	15.0	1.75	2.20	4.3
M14	34	40	53	18.0	2.00	2.50	5
M16	38	44	57	20.0	2.00	2.50	5
M18	42	48	61	20.0	2.50	3.20	6.3
M20	46	52	65	25.0	2.50	3.20	6.3
M24	54	60	73	30.0	3.00	3.80	7.5

nominal size	Length (l)	
	min.	max.
30	29.58	30.42
35	34.50	35.50
40	39.50	40.50
45	44.50	45.50
50	49.50	50.50
55	54.40	55.60

nominal size	Length (l)	
	min.	max.
60	59.40	60.60
65	64.40	65.60
70	69.40	70.60
80	79.40	80.60
90	89.30	90.70
100	99.30	100.70

nominal size	Length (l)	
	min.	max.
110	109.30	110.70
120	119.30	120.70
130	129.20	130.80
140	139.20	140.80

All technical data refer to the measure mm



DIN 939
Studs

Threaded end $\approx 1,25 d$

Steel 8.8 | zinc-plated | Cr(VI)-free | Metric thread

Diameter (d)	Length (l)															
	30	35	40	45	50	55	60	65	70	80	90	100	110	120	130	140
M6				●												
M8	●				●	●	●									
M10	●	●			●	●			●	●	●					
M12	●		●	●	●	●			●		●			●		●
M14					●	●		●								
M16		●			●		●		●			●			●	
M18																●
M20				●	●		●		●							
M24													●			

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

