


**ISO 4032** similar to DIN 934

## Hexagon nuts

Steel 5 - 2 | zinc-plated | Cr(VI)-free | Metric thread

Further information: ISO-standard has been withdrawn | changed spanner widths for M10, M12, M14 and M22 | changed head height | the fine thread has been transferred to ISO 8673



Diameter (d)	da		dw	e	m		s		Pitch (P)	Tool size
	min.	max.			min.	max.	min.	max.		
M8	8	8.75	11.6	14.38	6.44	6.8	12.73	13	1.25	SW 13
M10	10	10.80	14.6	17.77	8.04	8.4	15.73	16	1.50	SW 16
M12	12	13.00	16.6	20.03	10.37	10.8	17.73	18	1.75	SW 18
M16	16	17.30	22.5	26.75	14.10	14.8	23.67	24	2.00	SW 24
M20	20	21.60	27.7	32.95	16.90	18.0	29.16	30	2.50	SW 30
M24	24	25.90	33.3	39.55	20.20	21.5	35.00	36	3.00	SW 36
M30	30	32.40	42.8	50.85	24.30	25.6	45.00	46	3.50	SW 46
M33	33	35.60	46.6	55.37	27.40	28.7	49.00	50	3.50	SW 50
M36	36	38.90	51.1	60.79	29.40	31.0	53.80	55	4.00	SW 55

All technical data refer to the measure mm

