

RIVQUICK® Earthing rivets

with two fastons

Note: copper body and steel copper plated mandrel


Technical information can be found on the last page.

Diameter (d)	Article number	d ₁ nominal size	Drilling diameter d nominal size	e		Length (l) nominal size	Shear force (N)	Tensile force (N)
				min.	max.			
4	22194940003	4	5.3 - 5.4	0.8	1.5	6	1200	1700

All technical data refer to the measure mm



Symbol list



All technical data refer to the measure mm

